












ACC-166 Flap lining x2
A02


Note: 1.0mm (2.5oz) leather x1,
0.4mm regenerated leather x1















ACC-166 Handle surface leather x1
A05
Note: 1.0mm (2.5oz) leather is advised

www.leathercraftpattern.com



www.leathercraftpattern.com

ACC-166 Handle stiffener B x1
A06

Note: 2.0mm (5oz) leather is advised

ACC-166 Handle lining leather x1
A07

Note: 0.8mm (2oz) leather is advised

ACC-166 Bridge stiffener x1
B03

Note: 0.5mm vulcanized fibre is advised

ACC-166 A09 & A11 stiffener x2
B04

Note: 0.6mm regenerated leather is advised

www.leathercraftpattern.com

